









Rating	20A 12V DC	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		
Switch Function	4P DPST ON-OFF(Led Dependent)		



Material:
Frame: Black, Nylon 66
Actuator: Red, PC
Printed: None

Circuit Diagram



原稿
2017.11.13
研發部

Tolerances ± 0.3 Unless Otherwise Specified

10/20/17	曾敏捷	改善開關裝配強度,卡耳加膠加強,耳朵形狀變更			3	
9/20/12	張東	更新本體印刷,加SCI LOGO.			2	
6/27/07	曹盈芳	R13-244A8系列只通過UL,本體取消ENEC,增加T85,重新出圖.			1	
Date	Name	Description			No.	
Drawn	Checked	Approved	SCI BOM No.	1823924	Model Name	ROCKER SWITCH
曾敏捷	張東	曹盈芳	Customer No.		Model No.	R13-244B8-02
10/19/17	10/25-117	10/25-17	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 3