



Continuous Rating	100A 32VDC Max.	Mounting Hole  Panel Thickness:11.0mm Max.	Circuit Diagram	
Intermittent Rating	150 Amps		OFF	ON
Cranking Rating	500 Amps 5 sec.			
Contact Resistance	50m ohm Max			
Insulation Resistance	DC 500V 100M ohm Min			
Dielectric Strength	AC 1000V 1 minute, DC 2000V 1 minute			
Operation Temperature	-30°C~+60°C			
Switch Function	2P SPST OFF-ON			

Actuator can be taken out



***MATERIAL:**

Housing: Black, PA#66+33%GF
with White hot stamping

Actuator: Red, PBT+15%GF

Name Plate: White, ABS
with Black hot stamping

Bottom: Black, PBT+15%GF



Nut: Black, PA#66

Bolt: Brass

Hex Nut: Ni-plated, Brass

1 NUT ASSY

*Ingress Protection: IP56 for Panel seal



tolerances Unless otherwise specified ± 0.3

C3\WORK14\A23-7BO

3/25/'21	林玗呈	機種標示更新，原鑄離機種A23-7修改為鑄離機種A23-7BO(ECR#RAD20210303-095)							
Date	Name	Descriptions						NO	
Drawn	Checked	Approved	SCI BOM No.	1340085	Model Name	BATTERY SWITCH			
林玗呈	許庭碩	余啟明	Customer No.		Model No.	A23-7BO		REV.	
3/25/'21	2021/04/01	2021/04/01	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.				1