

Product Datasheet

Item No.: 10136

as
Schwabe
TechnikProdukte

PRODUCT NAME

Thermoplastic cable reel 25 m AT-N07V3V3-F 3G1,5 IP44



- IP44: protected against foreign bodies and splash-proof
- Reel body made from robust, shatterproof special plastic
- With stable, shock-absorbing and galvanized single-foot frame with parking brake
- Frame with ergonomically shaped handle and patented cable guide
- With built-in thermal circuit breaker
- With safety plug
- With 3 shock-proof socket outlets, splash-proof
- 230 V, 16 A, max. 3,500 W

Reference image

Technical data

EAN	4011160101366
Weight [kg]	4.99
Dimensions	19x38x28 cm
Main color	black
Category	Cable reels
Subcategory	Thermoplastic cable reels
Cable type	AT-N07V3V3-F
Cross section [mm ²]	3G1,5
Cable color	yellow
Cable length [m]	25
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	230 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44 with 25 m AT-N07V3V3-F 3G1,5
Output	3x shock-proof connector with red protective cap, socket insert, 230 V, 16 A, IP44
Total number of sockets	3
Number of Type F sockets (230 V)	3
Number of cores	3

Your partner for professional lighting and electrical products.