

Cable DisplayPort 1.2 female > DisplayPort female panel-mount 4K 60 Hz 0.25 m

Description

This cable by Delock can be used to extend an DisplayPort connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a DisplayPort connector in an easily accessible position.



Item no. 85113

EAN: 4043619851133

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x DisplayPort 20 pin female >
 - 1 x DisplayPort 20 pin female panel-mount
- DisplayPort 1.2 specification
- Pin 20 is connected (supports 3.3 V)
- Screw type: #4-40 UNC
- Mounting hole: ca. 18 x 7 mm, screw hole pitch ca. 27 mm
- Cable gauge: 30 AWG
- Cable diameter: ca. 6 mm
- Gold-plated connectors
- Transfer of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 25 cm

System requirements

- A free DisplayPort interface

Package content

- DisplayPort panel-mount cable
- 2 screws

Images



General

Specification:	DisplayPort 1.2
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort 20 pin female panel-mount
Connector 2:	1 x DisplayPort 20 pin female panel-mount

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Cable gauge:	30 AWG
Length:	25 cm
Colour:	black
Cable diameter:	6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de