




VSM 13328

Norma ritirata

4.8



BN 373

Viti a testa svasata piana ridotta

con intaglio

Acciaio 4.8

zincato bianco

 [3D Cadenas](#)


Tutte le misure con filettatura quasi completa
Realizzare la sede per testa svasata secondo la norma di riferimento!

Article#	d1	d2 theor.	d2 min.	k max.	n	t min.	L
1148982	M3	4,9	4,3	0,95	0,6	0,5	4
1148990							5
1149008							6
1149016							8
1149024							10
1149032							12
1149040							(14)
1149059							16
1149075							20
1149105	M4	6,4	5,8	1,2	0,8	0,6	5
1149113							6
1149121							8
1149148							10
1149156							12
1149172							16
1149199							20
1149210							25
1149229							30
1149237	M5	8,6	7,8	1,8	1	0,8	6
1149245							8
1149253							10
1149261							12
1149296							16
1149326							20
1149342							25
1149350							30

Article#	d ₁	d ₂ theor.	d ₂ min.	k max.	n	t min.	L
1149377	M5	8,6	7,8	1,8	1	0,8	40
1149385	M6	10,6	9,6	2,3	1,2	1	8
1149393							10
1149407							12
1149423							16
1149458							20
1149474							25
1149482							30