

TECHNICAL DATA

Producer	Qoltec
Maximum power	195W for PV 12V 390W for PV 24V
Rated voltage	12/24V
Rated current	15A
Maximum PV array open circuit voltage	<100V
MPPT efficiency	99%
Battery type	Compatible with AGM, GEL, LiFePO4
Safety	Short-circuit protection Overheating protection Overload protection Overcharge protection
Usage	Home photovoltaic systems Portable solar kits Solar systems in RVs and caravans Solar installations on boats and yachts Any location requiring efficient and reliable battery charging management
Additional information	USB output (5V/1A) Connectors 12AWG/4mm
IP rating	IP30
Operating temperature	-35°C ~ +55°C
Storage temperature	-30°C do +80°C
OTHER PARAMETERS	
Colour	Niebieski
Material	ABS, metal
Dimensions (D/L x W x H)	130 x 100 x 33mm
Package	Box
Package contents	1 x MPPT Controller 1 x User Manual 1 x Warranty card
Package depth / length [mm]	110
Package width [mm]	148
Package height [mm]	43
Net weight [kg]	0.287
Gross weight [kg]	0.326
Certificate	CE
Warranty	24 month
EAN code	5901878536668