


PoweredUSB cable male 12 V to DC 5.5 x 2.5 mm male 2 m

Description

This PoweredUSB cable by Delock can be used to supply power to a device with DC 5.5 x 2.1 mm female port via a PC or hub with PoweredUSB 12 V port.



Item no. 80496

EAN: 4043619804962

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x PoweredUSB male 12 V
 - 1 x DC 5.5 x 2.5 mm male
- PoweredUSB specification
- Voltage: 12 V
- Cable gauge: 20 AWG
- Cable diameter: ca. 4.2 mm
- Cable double shielded
- Cable jacket material: PVC
- Colour: black
- Length incl. connectors: ca. 2 m

Package content

- PoweredUSB cable

Images



PoweredUSB
12 V



DC 5,5 x 2,5 mm

General

Specification:	PoweredUSB
----------------	------------

Interface

Connector 1:	1 x PoweredUSB male 12 V
Connector 2:	1 x DC 5.5 x 2.5 mm male

Technical characteristics

Voltage:	12 V
----------	------

Physical characteristics

Cable gauge:	20 AWG
Shielding:	double
Length:	2 m
Colour:	black
Cable diameter:	4.2 mm
Cable jacket material:	PVC

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

