



Rating	15A Max. 12V DC		Circuit Diagram	
Contact Resistance	50M ohm Max.		OFF	
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1000V 1 minute			
Operation Temperature	-25°C~+85°C			
Switch Function	3P OFF-ON	Thickness:5.5mm max.		



Materials:
Frame: PBT, Black (UL flame: 94V-0)
Bottom: PBT, Black (UL flame: 94V-0)
Terminals: Copper Alloy
Contacts: Copper Alloy+AgSnO₂InO₃



Tolerances Unless Otherwise Specified ± 0.3

								⚠
								⚠
Date		Name	Description					NO
Drawn	Checked	Approved	SCI BOM No.			Model Name	KEY SWITCH	
Jam Chan			Customer No.			Model No.	K3-33A1-07	REV.
11/12/24			Unit	mm		SHIN CHIN INDUSTRIAL CO., LTD.		X0