

USB 2.0 Cable USB Type-C™ male to male PD 3.0 60 W 4 m black Silicone

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port.

Soft silicone cable jacket

The cable has a flexible, yet durable cable jacket made of pleasant-to-touch silicone. It does not get tangled or knotted when travelling, and its high flexibility protects against cable breakage even in everyday use.

USB Power Delivery (USB PD 3.0) support up to 60 watt

Support for the Extended Power Range resp. USB Power Delivery 3.0 standard means that connected devices can be supplied with power, up to 60 W (20 V / 3 A) is possible.



Item no. 81240

EAN: 4043619812400

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors: 2 x USB Type-C™ 2.0 male
- Cable gauge:
 - 28 AWG data line
 - 22 AWG power line
- Cable jacket material: Silicone
- Cable diameter: ca. 4 mm
- Contacts gold-plated
- Data transfer rate up to 480 Mbps
- USB Power Delivery (USB PD 3.0) support up to 60 watt (20 V / 3 A)
- Colour: black
- Length incl. connectors: ca. 4 m

Package content

- USB cable

Images



General

Specification:	USB 2.0 USB Power Delivery 3.0
Style:	both sides identical

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum power:	60 W
Maximum current:	3 A
Voltage:	20.0 V

Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 22 AWG power line
Length:	4 m
Colour:	black
Cable diameter:	4 mm
Cable jacket material:	silicone

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de