

USB Type-C™ Splitter (DP Alt Mode) > 1 x HDMI + 1 x DisplayPort out 4K 30 Hz

Description

This splitter by Delock is suitable for the connection of a DisplayPort monitor and an HDMI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Two monitors can be operated simultaneously at the outputs. The DisplayPort output is dual-mode capable (DP++), so that HDMI or DVI monitors can be connected with a suitable adapter.



Please Note

The product is a Multi-Stream-Transport (MST) hub and supports the extended desktop configuration of Displayport 1.2. When Mac OS is used, the same image is displayed on both ports (mirrored), it is not possible to use both ports independently of each other.

Item no. 87716

EAN: 4043619877164

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connectors:
Input: 1 x USB Type-C™ male
Output:
1 x HDMI-A 19 pin female
1 x DisplayPort 20 pin female
- Chipset: STDP4320
- DisplayPort 1.2 specification
- Resolution up to 2560 x 1440 @ 60 Hz / 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Active converter, Single / Multi Stream Transport Hub (SST / MST)
- Functions: Mirrored or Extended (Windows only)
- DisplayPort output supports Dual Mode DP++
- Transmission of audio and video signals
- USB bus powered
- Metal housing
- Colour: silver
- Cable length incl. connectors: ca. 10 cm
- Dimensions (LxWxH): ca. 73 x 60 x 15 mm


System requirements

- Windows 8.1/8.1-64/10/10-64, Mac ex OS 10.9
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ Splitter (DP Alt Mode)
- User manual

Images



General

Specification:	DisplayPort 1.2
Supported operating system:	Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	1 x DisplayPort female 1 x HDMI-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Kinetic STDP4320
Maximum screen resolution:	3840 x 2160 @ 30 Hz

Physical characteristics

Housing colour:	silver
Housing material:	metal
Cable length incl. connectors:	10 cm
Length:	73 mm
Width:	60 mm
Height:	15 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de