

HDMI to DVI 24+1 cable bidirectional 0.5 m

Description

This HDMI to DVI cable by Delock supports the data transfer in both directions. Thus it can be used to connect a DVI monitor or projector to the HDMI interface of a PC or laptop or to connect an HDMI monitor or projector to the DVI interface of a PC or laptop.



Item no. 85651

EAN: 4043619856510

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x High Speed HDMI-A 19 pin male >
 - 1 x DVI 24+1 male
- DVI connector with screws
- Cable gauge: 28 AWG
- Cable diameter: ca. 7.3 mm
- Contacts gold-plated
- Cable triple shielded
- Data transfer rate up to 7.92 Gb/s
- Resolution up to 2560 x 1600 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors (L): ca. 0.5 m

System requirements

- A free HDMI interface or
- A free DVI interface

Package content

- HDMI to DVI cable

Images



Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x DVI 24+1 male

Technical characteristics

Data transfer rate:	7.92 Gbps
Maximum screen resolution:	2560 x 1600 @ 60 Hz
Data transmission:	Bidirectional

Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	28 AWG
Shielding:	triple
Length:	50 cm
Colour:	black
Cable diameter:	7.3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de