

# Adapter USB 2.0 Type-A male to 1 x Serial RS-232 RJ45 male 1,8 m black

## Description

This USB 2.0 to RS-232 adapter by Delock is suitable for the console at CISCO routers, switches, access points and other compatible devices via PC or laptop.



1.8 m

**Item no. 64304**

EAN: 4043619643042

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:  
1 x USB 2.0 Type-A male  
1 x Serial RS-232 RJ45 male
- Chipset: FTDI FT232R
- Signals: CTS(1), DSR(2), RXD(3), GND(4), GND(5), TXD(6), DTR(7), RTS(8)
- Parity: even, odd, none, mark, space
- Stop bits: 1, 2
- Databits: 7, 8
- Flow control: none, Xon / Xoff, RTS / CTS
- FIFO: 128 Byte - RX
- FIFO: 256 Byte - TX
- Data transfer rate up to 230.4 Kb/s
- Cable length incl. connectors: ca. 1,8 m
- Suitable for various CISCO devices

## System requirements

- Linux Kernel 2.6 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

---

## Package content

- USB 2.0 to 1 x Serial adapter

---

## Images



## General

Function:	Plug & Play
Specification:	RS-232 (EIA / TIA) USB 1.1 USB 2.0
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11

## Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x RJ45 male

## Technical characteristics

Chipset:	FTDI FT232RL
Data transfer rate:	230.4 Kbps
FIFO:	128 byte 256 Byte
Data transmission:	asynchronous full duplex

## Physical characteristics

Cable length incl. connectors:	1.8 m
Colour:	black

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de