

Cable USB Type-C™ male > HDMI male (DP Alt Mode) 4K 30 Hz 2 m black

Description

This cable by Delock enables the connection of a HDMI monitor to a PC or laptop with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode.



Item no. 85259

EAN: 4043619852598

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB Type-C™ male >
1 x HDMI-A 19 pin male
- Chipset: Parade PS171 + Cypress
- High Speed HDMI with Ethernet (HEC) specification
- Signal direction: USB Type-C™ input > HDMI output
- Resolution up to 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Transfer of audio and video signals
- Supports 3D displays
- Supports HDCP 1.4
- USB bus powered
- Plug & Play
- Gold-plated connectors
- Colour: black
- Length without connectors: ca. 2 m

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64, Linux ex Kernel 4.x.x, Mac ex OS 10.12
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or

- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI cable

Images



General

Function:	Plug & Play
Specification:	HDCP 1.4 HDMI 1.4
Supported operating system:	Linux Kernel 4.x or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	1 x HDMI-A male
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Parade PS171 Cypress
Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio

Physical characteristics

Cable length:	2 m
Pin finishing:	gold-plated
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de