







CL31B226KPHNFN

Specifications

Property	Nominal Capacitance	Capacitance Tolerance	Rated Vdc	TCC	Size	Length	Width	Thickness
Value	22.0uF	±10%	10.0Vdc	X7R	1206(unit:inch), 3216(unit:mm)	3.20±0.20mm	1.60±0.20mm	1.60±0.20mm

Data Graph



Any data in this sheet are subject to change, modify or discontinue without notice. The data sheets include the typical data for design reference only. If there is any question regarding the data sheets, please contact our sales personnel or application engineers.