

Adapter USB Type-C™ male > HDMI female (DP Alt Mode) 4K 60 Hz

Description

This adapter by Delock is suitable for the connection of a HDMI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also operate on a Thunderbolt™ 3 interface.



Item no. 62978

EAN: 4043619629787

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x USB Type-C™ male >
1 x HDMI-A 19 pin female
- Chipset: Parade PS176
- DisplayPort 1.2 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 4096 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transfer of audio and video signals
- Supports 3D displays
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Dimensions incl. connector (LxWxH): ca. 48.0 x 22.5 x 10.3 mm
- Colour: black

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64, iPad Pro (2018), Linux ex Kernel 4.x.x, Mac ex OS 10.12
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI Adapter

General

Function:	Plug & Play
Specification:	DisplayPort 1.2 HDCP 1.4 HDCP 2.2 HDMI 2.0
Supported operating system:	Linux Kernel 4.x or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

Output:	1 x HDMI-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Parade PS176
Maximum screen resolution:	4096 x 2160 @ 60 Hz
Signal transmission:	video audio
Voltage supply:	USB bus powered

Physical characteristics

Length:	48.6 mm
Width:	22.5 mm
Height:	10.3 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de