

WiFi 6 Antenna RP-SMA plug 3 - 6 dBi omnidirectional with tilt joint black

Description

This Wireless LAN antenna can be connected to a WLAN device with RP-SMA interface, in order to send and receive signals.



Item no. 90677

EAN: 4043619906772

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors: 1 x RP-SMA plug
- Frequency range:
 - 2.4000 - 2.4835 GHz
 - 5.1500 - 5.8750 GHz
- Antenna gain: 3 - 6 dBi
- Impedance: 50 Ohm
- VSWR: 2.0:1
- Operating temperature: -10 °C ~ 55 °C
- Length:
 - ca. 201.0 mm (with tilt joint)
 - ca. 172.9 mm (without tilt joint)
- Width: ca. 20.0 mm
- Diameter: ca. 11.0 mm (RP-SMA)

System requirements

- Device with a free RP-SMA jack

Package content

- Antenna

Images



General

Mounting type:	Screw mounting
Suitable for indoor:	yes

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	2.4000 GHz - 2.4835 GHz 5.1500 GHz - 5.8750 GHz
Antenna gain:	3 - 6 dBi
Impedance:	50 Ohm
VSWR:	< 2.0

Physical characteristics

Antenna type:	dipol antenna
Width:	20.0 mm
Diameter connector:	11.0 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

