

USB Adapter 40 Gbps USB Type-C™ PD 3.1 240 W male to female angled left / right 8K 60 Hz

Description

This USB-C™ adapter by Delock can be used for the connection of USB-C™ devices. It can be also connected to a free USB-C™ port in order to prevent the interface from damage when it is under usage for high contact durability.



Item no. 60245

EAN: 4043619602452

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 40 Gbps USB Type-C™ male
 - 1 x USB 40 Gbps USB Type-C™ female
- Data transfer rate up to 40 Gbps
- USB Power Delivery (USB PD 3.1) support up to 240 watt
- Output current: up to 5 A
- Voltage: max. 48 V
- Supports DP Alt Mode
- Maximum resolution (depending on the system and the connected hardware):
 - DisplayPort 1.4 with DSC: up to 7680 x 4320 @ 60Hz
 - DisplayPort 1.4 with DSC: up to 3840 x 2160 @ 144 Hz
- Transmission of audio and video signals
- HDCP and HDR support
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3, Thunderbolt™ 4
- Useable on both sides
- Housing material: PVC
- Colour: anthracite
- Dimensions (LxWxH): ca. 2.7 x 1.2 x 0.7 cm

Package content

- USB adapter

General

Specification:	USB 40 Gbps
----------------	-------------

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ female

Technical characteristics

Operating voltage:	48 V
Data transfer rate:	40 Gbps

Physical characteristics

Housing material:	PVC
Length:	2.7 cm
Width:	1.2 cm
Height:	0.7 cm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de