

Coaxial USB Type-C™ to HDMI cable (DP Alt Mode) 4K 60 Hz with braided coating 1 m

Description

This cable by Delock enables the connection of a DisplayPort monitor to a device with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode. The coaxial cable is very flexible and easy to handle due to its small diameter.



Item no. 81703

EAN: 4043619817030

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI male
- Chipset: CS5265
- High Speed HDMI with Ethernet (HEC) specification
- Signal direction: USB Type-C™ input > HDMI output
- Cable gauge: 36 AWG
- Cable type: coaxial
- Cable diameter: ca. 3.5 mm
- With braided jacket
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Colour: black
- Length incl. connectors: ca. 1 m

Package content

- USB-C™ to HDMI cable

Images



General

Specification:	HDCP 1.4 HDCP 2.2 High Speed HDMI with Ethernet
----------------	---

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI male

Technical characteristics

Chipset:	CS5265
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	1 m
Pin finishing:	gold-plated
Cable gauge:	36 AWG
Shielding:	triple
Colour:	black
Cable diameter:	3.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de