

Keystone Module with 2 x USB Type-C™ Charging Port PD 20 W white

Description

This module by Delock provides two **USB Type-C™ Power Delivery (PD)** charging ports. The USB charging ports supports common fast charging protocols. Connected devices can be charged with **up to 20 W**. With its standardised dimensions it can be used for easy snap-in mounting in e.g. a Keystone patch panel, face plate or surface-mount box.



Item no. 41479

EAN: 4043619414796

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
2 x USB Type-C™ female
1 x 2 pin terminal block
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output power: max. 20.0 W total
USB-C™ 1: 5.0 V / 3.0 A, 9.0 V / 2.22 A, 12.0 V / 1.67 A
USB-C™ 2: 5.0 V / 3.0 A, 9.0 V / 2.22 A, 12.0 V / 1.67 A
USB-C™ 1 + USB-C™ 2: 5.0 V / 3.0 A
- Average active efficiency 86.8 %
- Efficiency at low load (10 %) 75.1 %
- No-load power consumption 0.1 W
- Short circuit protection
- For Keystone ports with 19.2 x 14.9 mm
- Colour: white
- Dimensions (LxWxH): ca. 44.7 x 41.2 x 32.5 mm

Package content

- Keystone module
- User manual

Images



General

Mounting type:	Keystone module
----------------	-----------------

Interface

Connector 1:	1 x 2 pin terminal block screw terminal
Connector 2:	2 x USB Type-C™ female

Physical characteristics

Length:	44,7 mm
Width:	41.2 mm
Height:	32.5 mm
Colour:	white

Power supply

Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.6 A
Power supply output:	12.0 V / 1.67 A / 20.0 W 5.0 V / 3.0 A 9.0 V / 2.22 A / 20.0 W

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

