

WiFi 7 Antenna N plug 2 - 3 dBi 20.6 cm omnidirectional with tilt joint and flexible material black

Description

This WLAN antenna by Delock allows the usage of different WLAN bands inside.



Item no. 90735

EAN: 4043619907359

Country of origin: Taiwan,
Republic of China

Package: White Box

Technical details

- Connector: 1 x N plug
- Frequency range:
2.400 - 2.500 GHz
4.900 - 7.125 GHz
- Antenna gain: 2 - 3 dBi
- Impedance: 50 Ohm
- VSWR: 2.0 - 3.0
- Polarisation: vertical
- HBW horizontal beamwidth: 360°
- VBW vertical beamwidth: 70° - 80°
- Transmission power: max. 2 W
- Operating temperature: -10 °C ~ 55 °C
- Housing material: ABS
- Colour: black
- Weight: ca. 41 g
- Dimensions (LxD): ca. 206 x 20 mm

System requirements

- Device with a free N port

Package content

- Antenna

General

Suitable for indoor:	yes
----------------------	-----

Interface

Connector:	1 x N male
------------	------------

Technical characteristics

Frequency range:	2400 - 2500 MHz 4800 - 7125 MHz
Antenna gain:	2 - 3 dBi
Beam width horizontal:	360°
Beam width vertical:	70° - 80°
VSWR:	2.0 - 3.0

Physical characteristics

Housing colour:	black
Housing material:	ABS UV resistant
Weight:	41 g
Dimensions (LxD):	20.6 x 2.0 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

