

Han 1A-base angled



Part number	09 10 000 0800
Specification	Han 1A-base angled
HARTING eCatalogue	https://b2b.harting.com/09100000800

Identification

Category	Hoods/Housings
Series	Han® 1A
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled

Version

Size	1 A
Details	Use 2x fixing screws M3

Technical characteristics

Limiting temperature	-30 ... +90 °C
Tightening torque	0.3 Nm Screws M3
Number of relockings	<10
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	TPE
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	IEC 61373 Category 1 Class B
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	12 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440202 Shell for industrial connectors