

Antenna cable F plug > SMB jack Bulkhead RG-316 25 cm

Description

This antenna cable by Delock enables the connection between radio frequency technology components.



Item no. 13025

EAN: 4043619130252

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x F plug
 - 1 x SMB jack bulkhead
- Thread length SMB jack: ca. 5 mm
- Impedance: 50 Ohm
- Cable category: coaxial
- Cable type: RG-316
- Cable attenuation: 0.9 dB @ 800 MHz per meter
- Cable diameter: 2.5 mm
- Minimum bending radius: 10.5 mm
- Colour: brown transparent
- Cable length incl. connectors: ca. 25 cm

System requirements

- Device with free F jack connector

Package content

- Antenna cable
- Locking ring

- Screw nut

Interface

Connector 1:	1 x F plug
Connector 2:	1 x SMB jack

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Thread length:	5 mm
Cable category:	coaxial
Cable type:	RG-316
Cable attenuation:	0.9 dB @ 800 MHz per meter
Cable colour:	brown transparent
Cable length incl. connectors:	25 cm
Pin finishing:	gold-plated
Smallest bending radius:	10.5 mm
Cable diameter:	2.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

