

Delock Extension cable USB 2.0 Type-A male > USB 2.0 Type-A female 2 m transparent

Description

This USB cable by Delock enables the extension of a USB 2.0 connection.



Item no. 83883

EAN: 4043619838837

Country of origin: China

Package: Zip poly bag

Technical details

- Connector:
USB 2.0 Type-A male >
USB 2.0 Type-A female
- 1 x ferrite core
- Cable gauge:
28 AWG data line
24 AWG power line
- Cable diameter: ca. 4 mm
- Cable double shielded
- Data transfer rate up to 480 Mb/s
- Colour: transparent
- Length: ca. 2 m

System requirements

- PC or laptop with a free USB Type-A port

Package content

- USB cable

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	USB 2.0 up to 480 Mb/s
---------------------	------------------------

Physical characteristics

Ferrite core:	1 x
Connector finishing:	nickel-plated
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 24 AWG power line
Shielding:	double
Length:	2 m
Colour:	transparent
Cable diameter:	4 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de