

Cable USB 2.0 Type-A male > USB 2.0 Type-A female panel-mount 1 m

Description

This cable by Delock can be used to extend an USB connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a USB connector in an easily accessible position.



Item no. 85106

EAN: 4043619851065

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB 2.0 Type-A female with nuts for installation
- Screw type: #4-40 UNC
- Mounting hole: ca. 15 x 8 mm, screw hole pitch ca. 30 mm
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 4.5 mm
- Gold-plated connectors
- Data transfer rate up to 480 Mb/s
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- A free USB interface

Package content

- USB panel-mount cable
- 2 screws

Images



General

Specification:	USB 2.0
----------------	---------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 24 AWG power line
Screw distance:	30 mm
Screw type:	#4-40 UNC
Length:	1 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de