



Technical Data

08.03.2021

HA47-HT - thick wall adhesive lined high temperature
Heat Shrinkable Tubing up to 4:1 - 1 m lengths

HA47-HT 48/12

Article Number 321-25004



Material: Polyolefin, chemically cross-linked (PO-X)

Colour: Black (BK)

Supplied $\emptyset$ D min.: 48.0 mm

Recov. $\emptyset$ d max.: 12.0 mm

Wall (WT): 4.1 mm

Shrink Ratio: up to 4:1

Longitudinal Change After Shrinkage: +/-10 % max

Min. Shrink Temperature - °C: +120 °C

Test Method

Operating Temperature - °C: -55 °C to +110 °C

Dielectric Strength: 20 kV/mm

ASTM D2671

Tensile Strength: 14 MPa

Elongation at break: 400%



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved