

Optical 4-button USB Gaming Mouse

Description

This wired USB gaming mouse by Delock, suitable for left and right handers, is ideal for operating computer games. The surface is made of a rubber coating for a comfortable feeling. By using the included software, there are several features supported, e.g. backlight, key function as well as different dpi-values up to 4800 dpi.



Item no. 12531

EAN: 4043619125319

Country of origin: China

Package: Retail Box

Technical details

- Connector: 1 x USB 2.0 Type-A male
- For right and left handers
- 2 standard buttons, 1 scroll wheel and 1 DPI button
- Settings:
 - dpi-value
 - backlight
 - programmable keys
 - scroll wheel
- Sensitivity:
 - 800 / 1200 / 1600 / 2400 dpi – DPI button
 - 3200 / 4800 dpi – Software setting
- Polling rate: 500 Hz
- Plug & Play
- Gold-plated connectors
- 1 x ferrite core
- Dimensions (LxWxH): ca. 132 x 69 x 39 mm
- Cable length: ca. 1.8 m
- Weight: ca. 148 g
- Colour: black / red

System requirements


- Windows 7/7-64/8.1/8.1-64/10/10-64

- PC or laptop with a free USB Type-A port

Package content

- Mouse
- CD ROM with software

Images



General

Style:	Right and left handers
--------	------------------------

Interface

Connector:	1 x USB 2.0 Type-A male
------------	-------------------------

Technical characteristics

Sensitivity:	800 / 1200 / 1600 / 2400 dpi – DPI button 3200 / 4800 dpi – Software setting
Polling rate:	500 Hz

Physical characteristics

Ferrite core:	1 x
Weight:	148 g
Cable length:	1.8 m
Connector finishing:	gold-plated
Length:	132 mm
Width:	69 mm
Height:	39 mm
Colour:	red black
Buttons:	2 standard buttons, 1 scroll wheel and 1 DPI button

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de