

# USB Retractable Cable Type-A to Lightning™ white / pale pink

## Description

This practical retractable cable by Delock can be connected to a PC or laptop with USB-A port and can be used to transfer data and charge the connected device.

### Useful companion

Due to its small size, the cable is a practical companion on the go and always at hand. A knotting of the cables is avoided by its winding mechanism.

### Flexible

The cable can be pulled out in five stages and thus offers different cable lengths, depending on requirements.



**Item no. 85817**

EAN: 4043619858170

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A male >
  - 1 x 8 pin Apple Lightning™ male
- Maximum output current: 2.1 A
- Voltage: max. 5 V
- Cable gauge:
  - 28 AWG data line
  - 24 AWG power line
- Flat cable
- Connector with metal housing
- Colour: white / pale pink
- Dimensions of housing (DxH): ca. 5.6 x 2.3 cm
- Length incl. connectors: ca. 92 cm (total incl. housing)
  - USB-A Host-cable ca. 46 cm
  - Lightning cable ca. 46 cm

## System requirements

- PC or laptop with a free USB Type-A port


---

## Package content

- Cable

---

## Images



## General

Specification:	USB 2.0
----------------	---------

## Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x Apple Lightning™ male

## Technical characteristics

Maximum current:	2.1 A
Voltage:	5 V

## Physical characteristics

Housing material:	metal
Cable length incl. connectors:	92 cm
Cable gauge:	28 AWG data line 24 AWG power line
Colour:	white pink

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

