



Model: **AK-SC-E04**



Product code	AK-SC-E04
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Number of phases	1 phase
Output amperage	32 A
Power supply connector	Type 2 (IEC 62196-2) Female Connector
Plated plugs	Silver
Product color	Blue
Product size (L x W x H)	220 x 95 x 75 mm
Package size (L x W x H)	225 x 100 x 77 mm
Net weight	419 g
Gross weight	425 g
EAN code	5901720136893



Description

Akyga® AK-SC-E04 plug will be ideal as a replacement for the damaged **Type 2 connector**. It is characterized by high resistance to drops. What's more, **silver plated connectors** with increased resistance allow to load the plug with a rated current of **32 A**. This makes it possible to use it in both **single-phase installations**. Or are you planning on replacing your old American-made electrician with a new European one? You have a wallbox with a Type 1 connector and need Type 2 (IEC62169-2)? No problem! Just change the plug for a new one!

Included with the plug is a **220 ohm resistor**, which is necessary for proper vehicle charging. Installation should be carried out by a suitably qualified person. Incorrect installation of the connector can cause material damage as well as loss of health or life (e.g. by electric shock).