


KEMET Part Number: C1206X475K3RACAUTO
(1206X475K3RACAUTO)

Ceramic, KEMET, AUTO-FlexTerm-(CxxxxX-AUTO), 4.7 uF, 10%, 25 V, 1206, X7R, SMD, MLCC, FT-CAP, Auto Grade



Dimensions

L	3.3mm +/-0.4mm
W	1.6mm +/-0.35mm
T	1.6mm +/-0.20mm
B	0.6mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information

Style:	SMD Chip
Supplier:	KEMET
Series:	AUTO-FlexTerm-(CxxxxX-AUTO)
Chip Size:	1206
Description:	SMD, MLCC, FT-CAP, Auto Grade
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Failure Rate:	N/A
AEC-Q200:	Yes
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	3.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	110 MOhms
Dielectric Strength:	62.5 V