DL4 Solar Cable 4 mm² male to female 1 m red

Description

This DL4 solar cable by Delock can be used to transmit power obtained from a photovoltaic system.

DL4 connectors

The DL4 plugs and sockets have a snap-in function, which avoids unwanted interruptions and ensures a secure connection. The connection can be released again with the appropriate tool.

IP67 dust and waterproof

The DL4 solar cable is protected from dirt and moisture.



Item no. 90972

EAN: 4043619909728

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x DL4 male
  1 x DL4 female
- Cable cross section: ca. 4 mm²
- Compatible with MC4, TS4, QC4
- Operating temperature: -40 °C ~ 90 °C
- Cable diameter: ca. 5 mm
- Protection class: IP67
- Voltage: max. 1000 V
- Colour: red
- Length incl. connectors: ca. 1 m

Package content


- DL4 cable

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Interface

Connector 1:	1 x DL4 male
Connector 2:	1 x DL4 female

Technical characteristics

Voltage:	1000 V

Physical characteristics

Length:	1 m
Colour:	red
Cable diameter:	5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**