





Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations. Tolerance specifications do not include clearances inherent in the design.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten. Bauartbedingtes Spiel ist in den Toleranzangaben nicht berücksichtigt.



Assembly example



General Information:

- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
- Further informationn see: www.phoenixcontact.com - item number

Additional Information:

- A. Mounting rail like EN 60715, TH 35-7,5 or mounting rail similar to EN 60715, TH 35-15x1,5
- B. 3D-CAD includes PCB-outline with TBUS item number 2202403
- C. Further TBUS options see item number 2202619 accessoires

KIT (not mounted)			
Pos.	QTY	Description	Item number
1	1	HOUSING with FOOT CATCH+FE CONTACT	2202619
2	1	HSC-LR 3U with SPRING	2201797
3	1	HEADER 2,5 2U	2201789
4	2	PLUG 2,5	2201780
5	2	CUC-SP-J1ST-A/R4LB-SMD	1149874
6	1	COVER for RJ45	1224119
7	1	COVER	2202630

 DIN A3	document-no. / ri		article-no.	scale	- Simplified representation - Document excluded from change process - Linear dimensions [mm]
	01394347 / 00		1342356	1:1	
	date	document-type			
	04.11.2021				
	description				
	ME-IO-KIT-MASTER 37,6 2RJ45				
page 1	of 1				