

Cable USB 2.0 Type-A male > USB 2.0 Micro-B female ShapeCable 0.35 m

Description

This cable by Delock can be used to connect USB devices with a Micro USB connector to the USB A port of a PC or laptop. An integrated wire in the ShapeCable can be bent into any form and retains its shape. This can be used to position the USB device in an optimal location.



Item no. 83921

EAN: 4043619839216

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: USB 2.0 Type-A male > USB 2.0 Type micro-B female
- ShapeCable: Integrated, shapeable wire
- Data transfer rate up to 480 Mbps
- Cable gauge: 28 AWG
- Cable diameter: ca. 4.8 mm
- Colour: black
- Length incl. connector: ca. 0.35 m

System requirements

- A free USB port

Package content

- USB 2.0 cable

General

Style:	ShapeCable
--------	------------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type Micro-B female

Technical characteristics

Data transfer rate:	USB 2.0 up to 480 Mb/s
---------------------	------------------------

Physical characteristics

Connector finishing:	nickel-plated
Pin finishing:	gold-plated
Cable gauge:	28 AWG
Length:	35 cm
Colour:	black
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de