

External 5 Gbps USB Hub with 10 Ports + Switch

Description

This solid USB hub by Delock with metal housing can be connected to a computer via the USB Type-A interface. It expands the computer by **10 USB Type-A ports**. Connected devices such as smartphones can be charged or data can be transferred at **5 Gbps**. Each port can be turned on or off individually by using the switches.



Item no. 63670

EAN: 4043619636709

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 10 x USB 5 Gbps Type-A female
 - 1 x 12 V DC jack
- Data transfer rate up to 5 Gbps
- 10 x LED indicator
- Robust metal housing
- Self-powered (works only with power supply)
- Dimensions (LxWxH): ca. 150 x 53 x 23 mm
- Colour: grey
- Plug & Play

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: SAW48-120-4000G
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 1.3 A
- Output voltage / Output current / Output power: 12.0 V / 4.0 A / 48.0 W
- Average active efficiency: 89.8 %
- Efficiency at low load (10 %): 87.6 %
- No-load power consumption: 0.07 W

- Power supply cable length: ca. 1.5 m
- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

System requirements

- Chrome OS
- Linux Kernel 5.8 or above
- Mac OS 10.15.6 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- Hub USB 5 Gbps
- 1 x cable USB 5 Gbps A male to USB 5 Gbps B male, length ca. 1 m
- Power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 5.8.0 or above Mac OS 10.15.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	10 x

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	10 x USB 5 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Cable length:	1 m
Material:	Aluminium
Length:	150 mm
Width:	53 mm
Height:	23 mm
Switch:	10 x
Colour:	grey

Power supply

Power supply type:	Power supply specification Euro wall power supply
Model identifier:	Power supply specification SAW48-120-4000G
Input voltage:	Power supply specification 100 - 240 V
Input AC frequency:	Power supply specification 50 / 60 Hz
Input current:	Power supply specification 1.3 A
Output voltage / Output current / Output power:	Power supply specification 12.0 V / 4.0 A / 48.0 W
Average active efficiency:	Power supply specification 89.8 %
Efficiency at low load (10 %):	Power supply specification 87.6 %
No-load power consumption:	Power supply specification 0.07 W
Power supply connector:	Power supply specification DC male 5.5 mm x 2.1 mm Ground outside, plus inside
Cable length of power supply:	Power supply specification 1.5 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de