



Click [here](#) for the 3D model.

Dimensions	
D	63mm MAX
H	35mm MAX
LL	15mm +/-2mm
S	20mm
S1	50mm
Wire Size	2.3mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	60
Typical Component Weight	205 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	4 mH (1 kHz)
Current	20 A
Temperature Range	-40/+105°C
DC Resistance	13 mOhms