

goodram

**RIVAL**

GAMING MICRO CARD

**GGSM2AA**

## MAIN FEATURES

UHS-I U3 interface  
 A2 performance-class  
 Available capacities: 64, 128, 256, 512 GB  
 Up to 170 MB/s read speed<sup>1</sup>  
 V30 Video Speed Class  
 The perfect storage expansion for handheld gaming consoles  
 Optimised for use with Android devices<sup>2</sup>  
 Lifetime warranty

**V30****A2**

Goodram RIVAL UHS-I U3 A2 microCARD is optimized for high-speed application performance. It's the ultimate solution for demanding handheld consoles, allowing you to expand your game library while maintaining the smooth, responsive gameplay you expect.

## + PARAMETERS

Available capacities	64, 128, 256, 512 GB
Card standard	Micro SDXC
Max. transfer	read: up to 170 MB/s, write: up to 120 MB/s <sup>1</sup>
Card dimensions	15.0 x 11.0 x 1.0 [mm]
Interface speed	UHS-I U3
Video Class Standard	V30
Performance-class	A2
Blister dimensions	103 x 123 [mm]
Operating temperature	-25°C to +85°C
Storage temperature	-40°C to +85°C

## + DETAILS

PRODUCT	CAPACITY	P/N	EAN
GOODRAM RIVAL M2AA	64 GB	GGSM2AA-0640R12	5908267914724
	128 GB	GGSM2AA-1280R12	5908267914748
	256 GB	GGSM2AA-2560R12	5908267914755
	512 GB	GGSM2AA-5120R12	5908267914779

<sup>1</sup>Based on internal tests using PCI-e adapter. Speed may vary depending on the testing methodology and platform and operating system.

<sup>2</sup>Card operation and performance will vary based on host device.

goodram

RIVAL

GAMING MICRO CARD

GGSM2AA



## LOGISTICS DATA

P/N	EAN	MOQ	PRODUCT DIMENSIONS (mm)	PRODUCT WEIGHT (g)	BLISTER DIMENSIONS (mm)	PRODUCT WEIGHT IN BLISTER (g)	MOQ CARTON DIMENSIONS (mm)	MOQ CARTON WEIGHT (g)	COLLECTIVE PACKAGING DIMENSIONS (mm)	COLLECTIVE PACKAGING WEIGHT (kg)
GGSM2AA-0640R12	5908267914724	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5
GGSM2AA-1280R12	5908267914748	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5
GGSM2AA-2560R12	5908267914755	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5
GGSM2AA-5120R12	5908267914779	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5