

USB4™ 40 Gbps Coaxial Cable 0.8 m

Description

This USB4™ cable by Delock enables the connection of various devices, such as smart phones, monitors, external enclosures and docking stations, via a USB Type-C™ or Thunderbolt™ 3 port of a PC or laptop. The cable supports the transfer of USB as well as DisplayPort and PCI Express data.

USB4™ 40 Gbps

The cable enables data transfer rates up to 40 Gbps when connecting USB4™-compatible devices. Of course, USB 3.2 or USB 2.0 devices can also be connected.

Connect DisplayPort monitors

The Delock cable supports DisplayPort 1.4a as well as DisplayPort 2.0 Alternate Mode, enabling the connection of DisplayPort monitors with a screen resolution up to 8K 60 Hz.

USB Power Delivery (USB PD 3.0) support up to 100 watt

Supports the USB Power Delivery 3.0 standard, which allows connected devices to be powered with up to 100 W (20 V / 5 A).



Item no. 86979

EAN: 4043619869794

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB4™ 40 Gbps (Gen 3x2) USB Type-C™ male >
1 x USB4™ 40 Gbps (Gen 3x2) USB Type-C™ male
- USB-IF certified cable
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3
- Chipset: Cypress E-Marker
- Cable type: coaxial
- Cable gauge:
30 AWG data line
24 AWG power line
- Contacts gold-plated
- Cable diameter: ca. 4.8 mm
- Data transfer rate up to 40 Gbps
- Display resolution up to:
7680 x 4320 @ 60 Hz
5120 x 2880 @ 120 Hz

3840 x 2160 @ 240 Hz
(depending on the system and the connected hardware)

- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Supports PCI Express 3.0 protocol
- Supports DisplayPort 1.4a protocol
- Supports DisplayPort Alt Mode 2.0
- Dual channel, bi-directional data transfer
- USB Power Delivery (USB PD 3.0) support up to 100 watt (20 V / 5 A)
- Colour: black
- Length incl. connectors: ca. 80 cm

System requirements

- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

Package content

- USB4™ 40 Gbps cable

Images



General

Specification:	DisplayPort 1.4 HDCP 1.4 HDCP 2.3 HDR10 PCI Express 3.0 USB 40 Gbps USB Power Delivery 3.0
Style:	both sides identical

Interface

Connector 1:	1 x USB4 Gen 3x2 Type-CTM male
Connector 2:	1 x USB4 Gen 3x2 Type-CTM male

Technical characteristics

Chipset:	Cypress E-Marker
Data transfer rate:	40 Gbps
Maximum screen resolution:	7680 x 4320 @ 60 Hz
Maximum power:	100 W
Maximum current:	5 A
Data transmission:	Bidirectional
Voltage:	20.0 V

Physical characteristics

Cable category:	coaxial
Cable gauge:	30 AWG data line 24 AWG power line
Length:	0.8 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de