

Mini DisplayPort to DisplayPort cable 8K 60 Hz 3 m grey metal without latch

Description

This DisplayPort cable by Delock is used to connect devices with a DisplayPort interface, such as monitors, projectors or televisions, to a PC or laptop with a mini DisplayPort interface.

8K resolution and HDR support

By supporting a maximum bandwidth of 32.4 Gbps, content up to 8K Ultra HD (7680 x 4320 @ 60 Hz) resolution can be displayed.

Due to the HDR support colours are realistically displayed with impressive depth, brightness and contrast are optimally reproduced.

Elegant metal housing and textile sheathing

Optically, the cable convinces with its elegant metal housings on the plugs and the textile sheathing around the cable jacket.



Item no. 81093

EAN: 4043619810932

Country of origin: CN

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort male
 - 1 x DisplayPort male
- Connector without latch
- DisplayPort 1.4 specification
- Downwards compatible to DisplayPort 1.3, 1.2 and 1.1
- Pin 20 not connected
- Connector with metal housing
- Cable with textile shielding
- Cable gauge: 30 AWG
- Cable diameter: ca. 6 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Connector finishing: gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 32.4 Gbps
- Resolution up to:
 - Display with DSC support:
 - 7680 x 4320 @ 60 Hz
 - 3840 x 2160 @ 240 Hz
 - Display without DSC support:
 - 7680 x 4320 @ 30 Hz

3840 x 2160 @ 120 Hz

(depending on the system and the connected hardware)

- Supports Display Stream Compression 1.2 (DSC)
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Supports HBR3 (8.1 Gbps) data rate
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format
- Colour: black / grey
- Length incl. connectors: ca. 3 m

Package content

- DisplayPort cable

Images



General

Cable finishing:	textile coating
Specification:	DisplayPort 1.4 HDCP 1.4 HDCP 2.3 HDR10
Style:	Connector without latch

Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x DisplayPort male

Technical characteristics

Data transfer rate:	32.4 Gb/s
Maximum screen resolution:	7680 x 4320 @ 60 Hz 3840 x 2160 @ 240 Hz

Physical characteristics

Housing material:	metal
Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Shielding:	triple
Length:	3 m
Colour:	grey black
Cable diameter:	6 mm

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de