Rev. 02_2026

PRODUCT CODE: PNR 5000 D

ESD C-shape forming pliers.



A special plier that cuts and forms the leads in one step.

The cutting length can be adjusted using the adjustable stop (min. 4 – max. 16).

For copper wire max Ø 0.8 mm (20 awg).

Forming force 3 kg.

Steel thickness 5 mm.

Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

ESD-safe version.

Made in Italy with special carbon steel and undergo a controlled atmosphere heat treatment.


The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin EVO handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

Laser marked.

Forming Plier Type	C-shape forming pliers
Copper wire	Max Ø 0.8mm (20 awg)
Forming force	3 Kg
Steel Thickness	5 mm
Material	High carbon steel
Length of the tool	150 mm +/- 2 mm
Net weight	105 g
ESD Safe	YES. Standard IEC 61340-5-1
Handle colour	grey/black

Rev. 02_2026


A
3.0
min max
A 4 16


PNR-5000
MADE IN ITALY
Cu Ø0.8 mm
PIERGIACOMI
QUALITY HAND TOOLS