

Han 2Mod Trägergehäuse



Part number	09 14 002 0311
Specification	Han 2Mod Trägergehäuse
HARTING eCatalogue	https://b2b.harting.com/09140020311

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Twin
Type of hood/housing	Carrier hood

Version

Locking type	Single locking lever
Size	Modular Twin

Technical characteristics

Limiting temperature	-40 ... +125 °C
Stripping length	10 mm PE contact
Tightening torque	1 Nm PE screw
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61984
----------------	-----------

Commercial data

Packaging size	1
Net weight	60.75 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors