This document was generated on 10/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0039000065
Status: Active
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel



Series image - Reference only

Documents:

Drawing (PDF)
Product Specification 55560002-PS-CH-000 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)
Product Specification 55560008-TS-000 (PDF)
Product Specification PS-54111-002-001 (PDF)
Product Specification PS-5556-001-001 (PDF)
Product Specification PS-5556-002-001 (PDF)
Application Specification 55560001-AS-000 (PDF)
Packaging Specification 55560001-PK-000 (PDF)
Test Summary 55560010-TS-000 (PDF)
Test Summary TS-5556-002-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000066 (Loose)
Product Name	Mini-Fit
Taxonomy	Crimp Terminals
UPC	800753584709

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	174.600/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	5556PBT2

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Packaging Specification	55560001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, 55560008-TS-000, PS-54111-002-001, PS-5556-001-001, PS-5556-002-001
Sales Drawing	55560000-SD-000

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
5556 Series

Use With
Mini-Fit Jr. Receptacle Housing 5557
Mini-Fit BMI Slide and Lock Panel Mount 44516
Mini-Fit BMI Panel Mount Receptacle Housing
 42474 , 43760

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	638191000

Test Summary	55560010-TS-000, TS-5556-002-001	

FineAdjust Applicator for Insulation OD 1.30-1.50mm, 22-28 AWG Wire	639002700
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG	639020200
FineAdjust Applicator for Insulation OD 0.95-1.08mm - 22-28 AWG	639023800
T2 Terminator for Insulation OD 1.30-1.50mm, 22-28 AWG	639102700
T2 Terminator for insulation OD 1.10-1.30mm - 22-28 AWG	639120200
T2 Terminator for insulation OD 0.95-1.08mm - 22-28 AWG	639123800