



Mi TS 30

- DIN rail
- DIN rail 35 x 15 mm, 284 mm long

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:
Suitable for box size:

Fastening material
1, 2, 3, 4, 6, 8

AMBIENT CONDITIONS

Application area:
Maximum ambient temperature 24 h:
Ambient temperature:
Relative humidity:

Indoor installation
35 °C
-5 °C up to +40 °C
≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:
Surface treatment:

Steel
Sendzimir galvanised

DIMENSIONS

Height:
Width:
Net weight:
Length:
Material thickness:

15 mm
35 mm
0.195 kg
284 mm
1.5 mm

CERTIFICATES

conforming to the standards:

DIN EN 60715, IEC 61439-2

SALES DATA

Product number: 2000015
EAN: 4012591650157
Pack unit: 1
Customs tariff number: 85371098
ETIM class: DYNAMIC: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-9.0: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-8.0: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-7.0: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-6.0: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-5.0: EC001285 - Mounting rail for electrical/industrial control equipment
ETIM-4.0: EC001285 - Mounting rail for electrical/industrial control equipment

DRAWINGS

