

USB Type-C™ Adapter to HDMI (DP Alt Mode) 4K 30 Hz - Key Chain

Description

This adapter by Delock is suitable for the connection of a HDMI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface. Due to the small dimensions, the adapter is ideal as on the go companion.



Item no. 63942

EAN: 4043619639427

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male >
 - 1 x HDMI-A 19 pin female
- Chipset: Realtek RTD2171U
- High Speed HDMI specification
- Resolution up to 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- USB bus powered
- Plug & Play
- Cable length without connectors: ca. 3 cm
- Colour: black

System requirements

- Android 6.0 or above
- Chrome OS
- iPad Pro (2018)
- Linux Kernel 4.3.3 or above
- Mac OS 10.13.3 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64

- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI adapter

Images



General

Function:	Plug & Play
Supported operating system:	Android 6.0 or above Chrome OS Linux Kernel 4.3.3 or above Mac OS 10.13.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

Output:	1 x HDMI-A female
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	Realtek RTD2171U VIA VL100
Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio

Physical characteristics

Colour:	black
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

Website www.delock.de