

5G 3.3 - 3.8 GHz Antenna N jack 8 dBi 50 cm omnidirectional fixed outdoor grey

Description

This antenna by Delock allows the usage of the 5G, 3,3 - 3,8 GHz band outdoors.



Item no. 90417

EAN: 4043619904174

Country of origin: China

Package: Box

Technical details

- Connector: 1 x N jack
- Frequency range: 3.3 - 3.8 GHz
- Antenna gain: 8 dBi
- Impedance: 50 Ohm
- VSWR: 2.0
- Polarisation: vertical
- Operating temperature: -40 °C ~ 80 °C
- Housing material: GFRP
- Colour: grey
- Dimensions (LxD): ca. 50 x 2.2 cm
- Thread diameter: ca. 15.5 mm

System requirements

- Device with a free N plug

Package content

- Antenna
- Mounting material

Images



General

Mounting type:	wall pole
Suitable for outdoor:	yes

Interface

Connector:	1 x N female
------------	--------------

Technical characteristics

Frequency range:	3.3 - 3.8 GHz
Antenna gain:	8 dBi
Beam width horizontal:	360°
Beam width vertical:	14°
Polarisation:	vertical
Transmission power:	50 W
VSWR:	2.0

Physical characteristics

Antenna type:	omnidirectional
Housing material:	GFRP
Colour:	grey
Dimensions (LxD):	50.0 x 2.2 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

