

19" Fibre Patch Panel 24 port LC Duplex blue

Description

This patch panel by Delock can be mounted in a 19" rack. The jacks on the front and rear of the panel provide convenient connections for fibre patch cable.



Item no. 43386

EAN: 4043619433865

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - 24 x LC Duplex female >
 - 24 x LC Duplex female
- Colour: blue
- For 48 OS2 Single-mode fibers
- Zirconia ceramic ferrule with protection cap
- For mounting in 19" racks, 1U
- Removable strain relief
- Housing colour: black
- Dimensions (LxWxH): ca. 482.6 x 150.0 x 43.6 mm

Package content

- 19" patch panel

General

Unit height:	1
Mounting type:	19 in
Style:	both sides identical

Physical characteristics

Housing colour:	black
Depth:	150 mm
Width:	482.6 mm
Height:	43.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

