

Adapter mini DisplayPort 1.2 male > DVI female 4K Active black

Description

This adapter by Delock enables the connection of an DVI monitor to the system via a free mini DisplayPort interface. The adapter supports a resolution up to 4K Ultra HD at 30 Hz and is backward compatible to Full-HD 1080p. The adapter offers an active conversion, thus it is also suitable for graphics cards that are not capable of outputting DP++ signals.



Item no. 62603

EAN: 4043619626038

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort 20 pin male
 - 1 x DVI 24+5 female with nuts
- Chipset: Parade PS171
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.2 specification
- Active converter, for graphics cards with DP and DP++ output
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Supports HDCP 1.3
- Supports Eyefinity
- Connectors: gold-plated
- 1 x ferrite core
- Cable length without connectors: ca. 20 cm
- Colour: black
- OS independent, no driver installation necessary

System requirements

- A free mini DisplayPort female

Package content

- Adapter

Images



General

Specification:	DisplayPort 1.2
----------------	-----------------

Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x DVI 24+5 female with nuts

Technical characteristics

Chipset:	Parade PS171
Maximum screen resolution:	3840 x 2160 @ 30 Hz

Physical characteristics

Ferrite core:	1 x
Cable length:	20 cm (without connector)
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de