

USB 2.0 Cable USB Type-A male to USB Type-C™ male with extended bend protection 2 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port.

Quality

Optically the cable convinces with its fine textile shielding and connectors with metal housing. The long kink protection provides better strain relief and protects against excessive bending.

Fast charging and power

The USB data and charging cable enables fast charging with its 60 W with a power bank or modern USB chargers. Quick Charge 3.0 is supported up to 20 V and 3 A.



Item no. 81122

EAN: 4043619811229

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB Type-A male
 - 1 x USB Type-C™ male
- Cable gauge:
 - 30 AWG data line
 - 22 AWG power line
- Fast Charging function: 20 V / 3 A (60 W)
- Cable diameter: ca. 4 mm
- Data transfer rate up to 480 Mbps
- Cable with textile shielding
- Connector with metal housing
- Colour: black
- Length: ca. 2 m

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0 USB Type-C™
----------------	------------------------

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	30 AWG data line 22 AWG power line
Length:	2 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de