



Model: **AK-SC-E03**



Product code	AK-SC-E03
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Number of phases	1 phase
Maximum current	32 A
Output connector	Type 2 (IEC 62196-2) Male Connector
Plated plugs	Silver
Product color	Blue
Product size (L x W x H)	240 x 110 x 45 mm
Package size (L x W x H)	245 x 115 x 47 mm
Net weight	380 g
Gross weight	386 g
EAN code	5901720136886



Description

The Akyga® AK-SC-E03 plug has a **Type 2 (IEC62169-2)** male connector also known as Mennekes. This is the most popular type of connector on the European Electric Vehicle market. It is used to connect the cable to the EVSE charging station. The old connector is worn out and no longer suitable for anything? No problem! Use this accessory to replace the damaged plug or to assemble your own electric vehicle charging cable. **The high quality construction** guarantees **resistance to drops and pressure**. What's more, **the silver-plated connectors** with increased resistance allow the plug to carry a current of **32 A**. This makes it possible to use it in both **single-phase installations**.

The installation should be done by a suitably qualified person. Incorrect installation of the connector may cause damage to property and loss of health or life (e.g. by electrocution).