









04P~15P



02P



03P



P/N LEGEND

A2013 H-XP N 0 X NP N 00 G
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- ① Series No.
- ② Connector type: H=Housing
- ③ No. of circuits
- ④ N=Halogen Free
- ⑤ Material: 0=Nylon 66-V0
- ⑥ Color: W=White ; B=Black
- ⑦ Plating code: NP=Non-plating
- ⑧ Plating code: N=Non-plating
- ⑨ Option code: 00=Standard
- ⑩ Packing code: G=Bag

SPECIFICATIONS

Current Rating: 4A AC,DC
Voltage Rating: 125V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 1000V AC/minute

Circuit No.	Dimensions		
	A	B	C
02P	2.00	6.00	4.80
03P	4.00	8.00	6.80
04P	6.00	10.00	8.80
05P	8.00	12.00	10.80
06P	10.00	14.00	12.80
07P	12.00	16.00	14.80
08P	14.00	18.00	16.80
09P	16.00	20.00	18.80
10P	18.00	22.00	20.80
11P	20.00	24.00	22.80
12P	22.00	26.00	24.80
13P	24.00	28.00	26.80
14P	26.00	30.00	28.80
15P	28.00	32.00	30.80



燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT SCALE SHEET
mm 1 : 1 1 of 1
DRAWN BY 郭木思
2013.02.16

TITLE:

2.00mm PITCH
HOUSING

APPROVED BY 謝瑞清
2013.02.16
GENERAL TOLERANCE
X.X±0.25
X.XX±0.15
X.XXX±0.05

DRAW NO.:
A2013H-XPNXXXXXXXXX

REV.
A2

REV.	DESCRIPTION	DATE	NAME
A2	EN202411071818	2024.11.07	樊翠鳳
A1	EN20220304968	2022.02.17	周傑亮
A0	NEW RELEASE	2013.02.16	郭木思