

# DisplayPort 1.2 extension cable 4K 60 Hz 2 m

## Description

This DisplayPort cable by Delock enables the extension of a DisplayPort connection. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.



**Item no. 80002**

EAN: 4043619800025

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:  
1 x DisplayPort male  
1 x DisplayPort female
- DisplayPort 1.2 specification
- Pin 20 is connected (supports 3.3 V)
- Cable gauge: 30 AWG
- Cable diameter: ca. 6 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz  
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 2 m

## System requirements

- A free DisplayPort interface

---

## Package content

- DisplayPort cable

---

## Images



## Interface

|              |                        |
|--------------|------------------------|
| Connector 1: | 1 x DisplayPort male   |
| Connector 2: | 1 x DisplayPort female |

## Technical characteristics

|                            |                     |
|----------------------------|---------------------|
| Data transfer rate:        | 21.6 Gbps           |
| Maximum screen resolution: | 3840 x 2160 @ 60 Hz |

## Physical characteristics

|                 |        |
|-----------------|--------|
| Cable gauge:    | 28 AWG |
| Length:         | 2 m    |
| Colour:         | black  |
| Cable diameter: | 7.3 mm |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |