

Coaxial USB 20 Gbps cable USB PD 3.0 60 W 3 m

Description

This USB cable by Delock enables the connection of various devices, such as smart phones, monitors, external enclosures and docking stations, via a USB Type-C™ or Thunderbolt™ 3 port of a PC or laptop. The cable supports the transfer of USB as well as DisplayPort and PCI Express data.



Item no. 81708

EAN: 4043619817085

Country of origin: China

Package: Zip poly bag

USB 20 Gbps

The cable enables data transfer rates up to 20 Gbps when connecting compatible devices. Of course, USB 3.2 or USB 2.0 devices can also be connected.

Connect DisplayPort monitors

The Delock cable supports DisplayPort 1.4a as well as DisplayPort 2.0 Alternate Mode, enabling the connection of DisplayPort monitors with a screen resolution up to 4K 144 Hz.

USB Power Delivery (USB PD 3.0) support up to 60 watt
Supports the USB Power Delivery 3.0 standard, which allows connected devices to be powered with up to 60 W (20 V / 3 A).

Technical details

- Connectors: 2 x USB 20 Gbps USB Type-C™ male
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3
- Chipset: E-Marker
- Cable gauge: 30 AWG
- Cable type: coaxial
- Cable diameter: ca. 4.8 mm
- Triple shielded cable
- Contacts gold-plated
- Data transfer rate up to 20 Gbps
- Display resolution up to:
3840 x 2160 @ 144 Hz
3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Supports PCI Express 3.0 protocol

- Supports DisplayPort 1.4a protocol
- Supports DisplayPort Alt Mode 2.0
- Dual channel, bi-directional data transfer
- USB Power Delivery (USB PD 3.0) support up to 60 watt (20 V / 3 A)
- Colour: black
- Length incl. connectors: ca. 3 m

Package content

- USB 20 Gbps cable

Images



General

Specification:	HDCP 1.4 HDCP 2.3 HDR10 PCI Express 3.0 Thunderbolt™ 3 USB 2.0 USB Power Delivery 3.0 DisplayPort 1.4a USB 3.2 DisplayPort Alt Mode 2.0
Style:	both sides identical

Interface

Connector 1:	1 x USB 20 Gbps USB Type-C™ male
Connector 2:	1 x USB 20 Gbps USB Type-C™ male

Technical characteristics

Chipset:	E-Marker
Data transfer rate:	up to 20 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz 3840 x 2160 @ 144 Hz

Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	3 m
Pin finishing:	gold-plated
Cable gauge:	30 AWG
Shielding:	triple
Colour:	black
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de